


Rittal – The System.

Faster – better – everywhere.



SG 2369.040

Steady light component

State: 29/01/2026 (Source: rittal.com/ro-ro)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SG 2369.040 - Steady light component for signal pillar, modular

With 360° signal transmission thanks to optimised prism system, number of potential stages = 5 components, with identical voltage.

Features

Model No.	SG 2369.040
Design	Steady light component
Product description	With 360° signal transmission thanks to optimised prism system. No. of potential stages = 5 components, with identical voltage.
Benefits	Simple assembly and contact via bayonet fastener. Configuration of up to five components with the same voltage. Components are available in a range of colours and voltages.
Function principle	A modular layout is possible with connection, optical and acoustic components, incandescent lamps and a label panel
Material	Enclosure of polyamide Cap: Transparent polycarbonate
Colour	Blue
Diameter	70 mm
Rated impulse withstand voltage, phase to phase	2500 V AC
Rated insulation voltage	250 V AC
Note on Model No.	Incandescent lamps not included with the supply.
Dimensions	Height: 56 mm
Protection category to IEC 60 529	IP 54 if a cover or acoustic component is fitted at the top
Rated operating voltage	12 V - 240 V (AC/DC)
Packs of	1 pc(s).
Net weight	0.079
Gross weight	0.08

Features

Customs tariff number	85311095
EAN	4028177219960
ECLASS 8.0	27371220

Approvals

Approvals	UL + C-UL (listed) UR
-----------	--------------------------