

Rittal – The System.

Faster – better – everywhere.



SG 2371.020 Flashing light component

State: 18/04/2026 (Source: rittal.com/ro-ro)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SG 2371.020 - Flashing light component for signal pillar, modular

With 360° signal transmission thanks to optimised prism system, number of potential stages = 5 components, with identical voltage.

Features

| | |
|---|--|
| Model No. | SG 2371.020 |
| Design | Flashing light component |
| Product description | With 360° signal transmission thanks to optimised prism system. Number of potential stages = 5 components, with identical voltage. |
| Benefits | Simple assembly and contact via bayonet fastener. Configuration of up to five components with the same voltage. Components are available in a range of colours and voltages. Flashing and stroboscopic light element incl. lamp, suitable for direct use. |
| Function principle | A modular layout is possible with connection, optical and acoustic components, incandescent lamps and a label panel |
| Material | Enclosure of polyamide Cap: Transparent polycarbonate |
| Colour | Yellow |
| Diameter | 70 mm |
| Rated impulse withstand voltage, phase to phase | 2500 V AC |
| Rated insulation voltage | 250 V AC |
| Rated current max. | 125 mA |
| Dimensions | Height: 56 mm |
| Protection category to IEC 60 529 | IP 54 if a cover or acoustic component is fitted at the top |
| Rated operating voltage | 24 V (DC) |
| Packs of | 1 pc(s). |

Features

| | |
|-----------------------|---|
| Net weight | 0,09 kg |
| Gross weight | 0,098 kg |
| Customs tariff number | 85311095 |
| ETIM 9 | EC000232 |
| ETIM 8 | EC000232 |
| ECLASS 8.0 | 27371220 |
| Product description | SG Flashing light component, for signal pillar, modular, 24 V DC, 125 mA, amber |

Approvals

| | |
|-----------|--------------------------|
| Approvals | UL + C-UL (listed) UR |
|-----------|--------------------------|