

Rittal – The System.

Faster – better – everywhere.



SG 2374.070

Incandescent lamps

State: 04/04/2026 (Source: rittal.com/ro-ro)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SG 2374.070 - Incandescent lamps for steady light components

With BA 15d base.

Features

Model No.	SG 2374.070
Product description	With BA 15d base.
Benefits	Simple assembly and contact via bayonet fastener.
Function principle	A modular layout is possible with connection, optical and acoustic components, incandescent lamps and a label panel
Power consumption (approx.)	5 W
Rated impulse withstand voltage, phase to phase	286 V AC
Rated insulation voltage	2000 V AC
Rated operating voltage	260 V
Packs of	3 pc(s).
Net weight	0,021 kg
Gross weight	0,024 kg
Customs tariff number	85392192
ETIM 9	EC000232
ETIM 8	EC000232
ECLASS 8.0	27371220
Product description	SG Incandescent lamp, for steady light component, 230 V, 5W