

**Rittal – The System.**

Faster – better – everywhere.



# SZ 2411.851

## Cable gland, brass

State: 07/07/2026 (Source: [rittal.com/ro-ro](http://rittal.com/ro-ro))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SZ 2411.851 - Cable gland, brass

Integrated clamping membrane ensure safe tightening and cable-friendly strain relief.

## Features

Model No.	SZ 2411.851
Benefits	Because the gland and lock nut are sold together in a single pack, this saves additional ordering and storage. Clamping membranes for even tightening and strain relief to protect the cables
Material	Brass Seal: CR/NBR
Surface finish	Nickel-plated
IP protection category to IEC 60529	IP 68 (5 bar, 30 min)
Dimensions	Height: 43 mm
Thread	M40 x 1.5
Thread length	9 mm
Min. cable diameter	19 mm
Max. cable diameter	28 mm
Operating temperature range	-40 °C...100 °C
torque	17 Nm
Width across flats	43 mm
Dimensions	Thread: M40 x 1.5 Thread length: 9 mm
Type rating to UL 50E	Type 1 Type 4 Type 4X Type 12 Type 13
Packs of	4 pc(s).

# Features

---

Net weight	0,64 kg
Gross weight	0,692 kg
Customs tariff number	74198090
ETIM 9	EC000441
ETIM 8	EC000441
ECLASS 8.0	27149109
Product description	SZ Cable gland, brass, size: M40x1,5, for cables ø 19-28 mm

---

# Approvals

---

Approvals	UL + C-UL (listed) VDE
Explanations	Declaration of conformity Declaration of conformity UK

---