

# Rittal – The System.

Faster – better – everywhere.



## AX 2537.100

## Mini-comfort handle AX

State: 07/07/2026 (Source: [rittal.com/ro-ro](http://rittal.com/ro-ro))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# AX 2537.100 - Mini-comfort handle AX

The lock is opened by swivelling the unlocked handle.



## Features

|                       |   |
|-----------------------|---|
| Model No.             | AX 2537.100   |
| Design                | For lock inserts and semi-cylinders   |
| Product description   | The unlocked handle folds out forwards, and the lock is opened by swivelling. Prepared for the installation of profile half-cylinders and lock inserts (to DIN 18 252). ASSA and KESO/KABA version prepared for profile half-cylinders. |
| Material              | Die-cast zinc<br>Plastic  |
| Surface finish        | Powder-coated   |
| Colour                | RAL 7035  |
| Lock                  | Lock version: Prepared for lock inserts, version A, the installation of profile semi-cylinders with an overall length of 40 or 45 mm (to DIN 18 252) or lock and push-button inserts with a length of 40 mm                             |
| To fit enclosure type | AX with sheet steel cam<br>AX IT with cam lock<br>KX E-Box<br>VX partial door<br>CX one-piece console<br>Console CX<br>CX desk unit   |

# Features

---

|                       |  |
|-----------------------|--|
| Type rating to UL 50E | Type 1<br>Type 3R<br>Type 4<br>Type 12   |
| Packs of              | 1 pc(s).   |
| Net weight            | 0,29 kg  |
| Gross weight          | 0,3 kg   |
| Customs tariff number | 83024110   |
| ETIM 9                | EC000327   |
| ETIM 8                | EC000327   |
| ECLASS 8.0            | 27189266   |
| Product description   | AX Mini-comfort handle, for AX and KX with cam, for lock inserts or semi-cylinders |

# Approvals

---

|           |                         |
|-----------|-------------------------|
| Approvals | DNV<br>UL + C-UL - FTTA |
|-----------|-------------------------|