

# Rittal – The System.

Faster – better – everywhere.



## SZ 2563.100 Metal gland plate

State: 22/05/2026 (Source: [rittal.com/ro-ro](http://rittal.com/ro-ro))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SZ 2563.100 - Metal gland plate with metric knockouts

Simply knock out the holes for the cable glands using a screwdriver, IP 66 when mounting in the usual position at the bottom.

## Features

|                                   |   |
|-----------------------------------|---|
| Model No.                         | SZ 2563.100   |
| Product description               | Simply knock out the holes for the cable glands using a screwdriver.        |
| Material                          | Sheet steel   |
| Colour                            | RAL 7035  |
| Note                              | The allocation of gland plate sizes is indicated on the relevant enclosures |
| No. of metric knockouts           | 1 x M12<br>12 x M20<br>11 x M25<br>8 x M32<br>4 x M40                       |
| Dimensions                        | Width: 534 mm<br>Depth: 149 mm  |
| To fit                            | Enclosure type: AE  |
| Gland plate                       | Size: 5   |
| Protection category to IEC 60 529 | IP 66 when mounting in the usual position at the bottom                     |
| Packs of                          | 1 pc(s).  |
| Net weight                        | 0,96 kg   |
| Gross weight                      | 1,004 kg  |
| Customs tariff number             | 73079100  |
| ETIM 9                            | EC000211  |
| ETIM 8                            | EC000211  |
| ECLASS 8.0                        | 27142421  |

# Features

---

Product description

SZ Metal gland plate, with metric knock-outs, WD: 534x149 mm,  
size: 5