Rittal - The System.

Faster – better – everywhere.






SZ 2564.200 Plastic gland plate, modular

State: 29/10/2025 (Source: rittal.com/ro-ro)



SZ 2564.200 - Plastic gland plate, modular with metric knockouts, for AX

Simply break through the plastic on the knockouts for cable glands. Additional rectangular cutouts and reinforcement frame allow the cable gland to be installed directly (modular).







Features

Model No.	SZ 2564.200
Product description	Simply break through the plastic on the knockouts for cable glands. Additional rectangular cut-outs and reinforcement frame allow the cable gland to be installed directly (modular).
Material	Plastic to UL 94-V0
Colour	RAL 7035
Number of rectangular cutouts information	1 rectangular cut-out can hold 10 small seal inserts
Number of rectangular cutouts	6
Note	The allocation of gland plate sizes is indicated on the relevant enclosures
No. of metric knockouts	5 x M12 4 x M16 6 x M20 5 x M25 1 x M32 1 x M40

© Rittal 2025 2

Features

Dimensions	Width: 534 mm
	Depth: 149 mm
To fit	Enclosure type: AX
Gland plate	Size: 4
Operating temperature range	-40 °C80 °C
Protection category to IEC 60 529	IP 66 if installed correctly
Type rating to UL 50E	Type 1
	Type 12
Number knockouts	5
	4
	6
	5
	1
	1
Metric diameter	M12
	M16
	M20
	M25
	M32
	M40
Packs of	1 pc(s).
Net weight	0.54
Gross weight	0.573
Customs tariff number	39269097
EAN	4028177938427
ETIM 9	EC000211
ETIM 8	EC000211
ECLASS 8.0	27142421

Approvals

© Rittal 2025 3

Approvals

Approvals

UL + C-UL - FTTA

© Rittal 2025 4