

# Rittal – The System.

Faster – better – everywhere.



## TP 2684.600 One-piece consoles

State: 29/08/2025 (Source: [rittal.com/ro-ro](http://rittal.com/ro-ro))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# TP 2684.600 - One-piece consoles Stainless steel

Stainless steel one-piece consoles 1.4301, (AISI 304), ready-to-use unit with high protection category IP 55 in four different widths. Easy handling thanks to self-latching lid stay. Interchangeable lock insert. Easy cable entry thanks to divided gland plates



## Features

|                                   |   |
|-----------------------------------|---|
| Model No.                         | TP 2684.600   |
| Material                          | Enclosure: Stainless steel 1.4301 (AISI 304), 1.5 mm<br>Door or double door and console lid: Stainless steel 1.4301 (AISI 304), 2.0 mm<br>Mounting plate: Sheet steel, 3.0 mm   |
| Surface finish                    | Enclosure, door, console lid and gland plates: Brushed, grain 400<br>Mounting plate: Zinc-plated  |
| Supply includes                   | Enclosure, solid back and sides<br>Door or double door at front, with locking rod<br>Console lid with lid stay and cam lock latched in the enclosure<br>Locks with double-bit insert<br>Gland plates, divided<br>Mounting plate |
| Dimensions                        | Width: 800 mm<br>Height: 960 mm   |
| Dimensions mounting plate (W x H) | 730 mm x 780 mm   |
| Depth (top)                       | 480 mm  |

## Features

|                                     |  |
|-------------------------------------|--|
| Depth (bottom)                      | 400 mm   |
| Number of doors                     | 1  |
| IP protection category to IEC 60529 | IP 55  |
| Protection category NEMA            | NEMA 12  |
| Basic material                      | Stainless steel 1.4301 (AISI 304)  |
| Dimensions                          | Width: 800 mm<br>Height: 960 mm<br>Depth (top): 480 mm<br>Depth (bottom): 400 mm |
| Packs of                            | 1 pc(s).   |
| Net weight                          | 60   |
| Gross weight                        | 65.2   |
| Customs tariff number               | 94032080   |
| EAN                                 | 4028177031357  |
| ETIM 9                              | EC000784   |
| ETIM 8                              | EC000784   |
| ECLASS 8.0                          | 27180504   |

## Approvals

|              |   |
|--------------|---|
| Approvals    | TÜV<br>UL + C-UL (listed)                                 |
| Explanations | Declaration of conformity<br>Declaration of conformity UK |