

Rittal – The System.

Faster – better – everywhere.



TP 2695.500

Universal consoles TP

State: 10/06/2026 (Source: rittal.com/ro-ro)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



TP 2695.500 - Universal consoles TP

Universal consoles TP, high level of stability and protection category IP 55 because the body is more or less manufactured from a single piece. Flexible front design, optionally with drawers or desk section. Easy accessibility thanks to divided doors. Interchangeable lock insert.

Features

| | |
|-------------------------------------|--|
| Model No. | TP 2695.500 |
| Design | with tall front door |
| Product modification | The universal console comes with the new mounting plate of the baying enclosure system VX25. |
| Material | Enclosure, gland plates: Sheet steel 1.5 mm Door: Sheet steel, 2.0 mm Mounting plate: Sheet steel, 3.0 mm |
| Surface finish | Enclosure and door: Dipcoat primed, powder-coated on the outside, textured paint Mounting plate and gland plates: Zinc-plated |
| Colour | RAL 7035 |
| Supply includes | Enclosure with door(s) Mounting plate Gland plates |
| Dimensions | Width: 600 mm Height: 1,300 mm |
| Dimensions mounting plate (W x H) | 499 mm x 1,196 mm |
| Depth (top) | 417,5 mm |
| Depth (bottom) | 500 mm |
| IK Code | IK08 |
| Note | For universal console with short front door: The desk section should be fitted in order to maintain the protection category. |
| IP protection category to IEC 60529 | IP 55 |

Features

| | |
|--------------------------|--|
| Protection category NEMA | NEMA 12 |
| Basic material | Sheet steel |
| Dimensions | Width: 600 mm Height: 1,300 mm Depth (top): 417.5 mm Depth (bottom): 500 mm |
| Packs of | 1 pc(s). |
| Net weight | 74,1 kg |
| Gross weight | 78 kg |
| Customs tariff number | 94032080 |
| ETIM 9 | EC000784 |
| ETIM 8 | EC000784 |
| ECLASS 8.0 | 27180504 |
| Product description | TP Universal console, WHD: 600x1300x500 mm, Sheet steel, with tall front door |

Approvals

| | |
|--------------|---|
| Approvals | TÜV UL + C-UL (listed) |
| Explanations | Declaration of conformity Declaration of conformity UK |