### Rittal – The System.

Faster – better – everywhere.






# FT 2760.010 Viewing window

State: 11/11/2025 (Source: rittal.com/ro-ro)



## FT 2760.010 - Viewing window for AX

For external mounting on AX enclosures instead of a door and on surfaces.







#### **Features**

Model No.	FT 2760.010
Design	60 section
Product description	For external mounting on AX enclosures instead of a door and on surfaces.
Material	Frame: Aluminium, natural anodised. Glass panel: Acrylic
Supply includes	Plastic handle with lock insert no. 3524 E
Protection category to IEC 60 529	IP 54
To fit Model No.	1039.000 1339.000 1009.000
To fit	Enclosure type: AX Width: = 600 mm Height: = 380 mm
Dimensions	Width: 597 mm Height: 377 mm Depth: 62 mm
Visible area	Viewing window width: 537 mm Viewing window height: 317 mm

© Rittal 2025

#### **Features**

Build depth for components (max.)	58 mm
Packs of	1 pc(s).
Net weight	3.245
Gross weight	3.3
Customs tariff number	76101000
EAN	4028177938571
ETIM 9	EC002527
ETIM 8	EC002527
ECLASS 8.0	27182204

© Rittal 2025 3