

Rittal – The System.

Faster – better – everywhere.



SK 3236.124

Mini fan

State: 10/04/2026 (Source: rittal.com/ro-ro)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SK 3236.124 - Mini fan

Compact DC fan for enclosure and component cooling in enclosures.

Features

| | |
|-----------------------------|---|
| Model No. | SK 3236.124 |
| Product description | Compact DC fan for enclosure and component cooling in enclosures. |
| Supply includes | Fan Assembly screws Contact hazard protection |
| Rated operating voltage | 24 V (DC) |
| Power consumption Pel | With DC: 1 W |
| Dimensions | Width: 60 mm Height: 60 mm Depth: 25.4 mm |
| Note | Electrical connection via 2 single wires (length approx. 300 mm) |
| Operating temperature range | -20 °C...70 °C |
| Noise level | With DC: 20 dB(A) |
| Packs of | 1 pc(s). |
| Net weight | 0,11 kg |
| Gross weight | 0,12 kg |
| Customs tariff number | 84145915 |
| ETIM 9 | EC000320 |
| ETIM 8 | EC000320 |
| ECLASS 8.0 | 27180716 |
| Product description | SK Mini fan, 1 W, 24 V (DC), WHD: 60 x 60 x 25.4 mm |

Approvals

Approvals

UR

Explanations

Declaration of conformity