Rittal – The System.

Faster – better – everywhere.





SK 3301.500 Electric condensate evaporator

State: 14/12/2025 (Source: rittal.com/ro-ro)



SK 3301.500 - Electric condensate evaporator

For external mounting on the enclosure. For use with all enclosure cooling units and air/water heat exchangers (wall-mounted).



Features

Model No.	SK 3301.500
Product description	For external mounting on the enclosure. For use with all enclosure cooling units and air/water heat exchangers (wall-mounted).
Benefits	Suitable for international use thanks to multi-voltage support
Colour	RAL 7035
Supply includes	Electric condensate evaporator, ready to connect.
Evaporation performance	230 V: 3,5 I/d
	115 V: 3.0 I/d
Dimensions	Width: 280 mm
	Height: 129 mm
	Depth: 105 mm
Operating temperature range	5 °C60 °C
Rated operating voltage	115 V - 230 V, 1~, 50 Hz/60 Hz
Packs of	1 pc(s).
Net weight	1.32
Gross weight	1.72
Customs tariff number	84159000
EAN	4028177695511

© Rittal 2025 2

Features

ETIM 9	EC002009	
ETIM 8	EC002009	
ECLASS 8.0	27180715	

Approvals

Certificates	EAC
Explanations	Declaration of conformity

© Rittal 2025 3