

**Rittal – The System.**

Faster – better – everywhere.



# SV 3555.000

## Conductor connection clamp

State: 13/05/2026 (Source: [rittal.com/ro-ro](http://rittal.com/ro-ro))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 3555.000 - Conductor connection clamp

For connecting round conductors and laminated copper bars.

## Features

Model No.	SV 3555.000
Product description	For connecting round conductors and laminated copper bars.
Material	Brass
Note	Wire end ferrules should be used with fine wire conductors
Connection of round conductors	1 - 4 mm <sup>2</sup>
For bar thickness	6 - 10 mm
Packs of	15 pc(s).
Net weight	0,345 kg
Gross weight	0,401 kg
PCF per pack (cradle-to-gate)	1.5 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Customs tariff number	85369010
ETIM 9	EC000001
ETIM 8	EC000001
ECLASS 8.0	27141146
Product description	SV Conductor connection clamp, 1-4 mm <sup>2</sup> , for bar thickness 6-10 mm, brass

## Approvals

Explanations	Declaration of conformity Declaration of conformity UK
--------------	---

# Tender text

SV conductor connection clamps

for E-Cu busbars and Rittal PLS.

for bar thickness: 10 mm

Connection: for round conductors 1 - 4 mm<sup>2</sup>

Wire end ferrules should be used with fine wire conductors.

Tightening torque

Conductor connection clamp: 2 Nm

Material: brass