

**Rittal – The System.**

Faster – better – everywhere.



# SV 3555.000 Conductor connection clamp

State: 04/07/2026 (Source: [rittal.com/ro-ro](http://rittal.com/ro-ro))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 3555.000 - Conductor connection clamp

For connecting round conductors and laminated copper bars.

## Features

|                                |  |
|--------------------------------|--|
| Model No.                      | SV 3555.000  |
| Product description            | For connecting round conductors and laminated copper bars.   |
| Material                       | Brass  |
| Note                           | Wire end ferrules should be used with fine wire conductors   |
| Connection of round conductors | 1 - 4 mm <sup>2</sup>  |
| For bar thickness              | 6 - 10 mm  |
| Packs of                       | 15 pc(s).  |
| Net weight                     | 0,345 kg   |
| Gross weight                   | 0,401 kg   |
| PCF per pack (cradle-to-gate)  | 1.5 kg CO2 eq (Cat B)  |
| Note on PCF category           | Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared |
| Customs tariff number          | 85369010   |
| ETIM 9                         | EC000001   |
| ETIM 8                         | EC000001   |
| ECLASS 8.0                     | 27141146   |
| Product description            | SV Conductor connection clamp, 1-4 mm <sup>2</sup> , for bar thickness 6-10 mm, brass                          |

## Approvals

|              |   |
|--------------|---|
| Explanations | Declaration of conformity<br>Declaration of conformity UK |
|--------------|---|

# Tender text

SV conductor connection clamps

for E-Cu busbars and Rittal PLS.

for bar thickness: 10 mm

Connection: for round conductors 1 - 4 mm<sup>2</sup>

Wire end ferrules should be used with fine wire conductors.

Tightening torque

Conductor connection clamp: 2 Nm

Material: brass