


**Rittal – The System.**

Faster – better – everywhere.



# AS 4050.742

## Wire end ferrules

State: 28/01/2026 (Source: [rittal.com/ro-ro](http://rittal.com/ro-ro))

# AS 4050.742 - Wire end ferrules loose

With plastic collar.

## Features

Model No.	AS 4050.742
Product description	With plastic collar.
Technical specifications	Heat-resistant to 105 °C
Material	E-Cu, galvanic tin-plated Plastic collar: Polypropylene
Colour	White
Length	8 mm
AWG	20
Internal diameter	2,9 mm
For cross-section	0,5 mm <sup>2</sup>
DIN colour code	Yes
Multinorm	Yes
Note	UL-certified in conjunction with the relevant tools, such as crimping machines. For bespoke advice, please contact your Rittal sales consultant.
Delivery form	Loose
Packs of	500 pc(s).
Net weight	0.5
Gross weight	0.5
Customs tariff number	85369010
EAN	4028177805101
ETIM 9	EC000005
ETIM 8	EC000005

# Features

---

ECLASS 8.0 36659290

---

## Approvals

---

Approvals UL + C-UL (listed)  
UR