

Rittal – The System.

Faster – better – everywhere.



AS 4051.020

Crimping machine RC-I

State: 23/07/2026 (Source: rittal.com/ro-ro)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE


SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4051.020 - Crimping machine RC-I for Wire Terminal WT 24/36

Crimping machine with 5-way magazine for processing insulated wire end ferrules on a reel. This device has an interface to communicate with the Rittal Wire Terminal fully automated wire processing machine and supports complete functional integration. Training course 5058.207 must additionally be purchased for this item.



Features

Model No.	AS 4051.020
Product description	Crimping machine with 5-way magazine for processing insulated wire end ferrules on a reel. This device has an interface to communicate with the Rittal Wire Terminal fully automated wire processing machine and supports complete functional integration. Training course 5058.207 must additionally be purchased for this item.
Benefits	No changing of the wire end ferrules required due to 5-way magazine
Technical specifications	Cross-sections ranging from 0.5–2.5 mm ² (AWG 20-14) Crimping length 8 and 10 mm Insertion length 27 mm (1.06 in.)
To fit Model No.	4051024 4051036
Packs of	1 pc(s).
Net weight	22 kg
Gross weight	22,5 kg

Features

Customs tariff number	84633000
ETIM 9	EC002778
ETIM 8	EC002778
ECLASS 8.0	17130101
Product description	AS Crimping machine RC-I, for Wire Terminal