


Rittal – The System.

Faster – better – everywhere.



AS 4054.002 Crimping pliers

State: 28/08/2025 (Source: rittal.com/ro-ro)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4054.002 - Crimping pliers for wire end ferrules

Crimping tool for square or hexagonal compression, for processing wire end ferrules with no insulating collar to DIN 46228, Part 1 and wire end ferrules with insulating collar to DIN 46228, Part 4.

Features

| | |
|--------------------------|--|
| Model No. | AS 4054.002 |
| Design | Straight |
| Product description | For use with wire end ferrules with no insulating collar to DIN 46228, Part 1 and wire end ferrules with insulating collar to DIN 46228, Part 4. |
| Benefits | Minimal effort required with large wire cross-sections Uniformly high quality compression Releasable ratchet Self-adjusting |
| Material | High-quality special tool steel |
| Surface finish | Matt, plated |
| Colour | null |
| Compression | Square crimp |
| Direction of cable entry | Side |
| Dimensions | Length: 176 mm |
| AWG | 26 - 8 |
| For cross-section | 0.14 - 10 mm ² |
| Packs of | 1 pc(s). |
| Net weight | 0.4 |
| Gross weight | 0.449 |
| Customs tariff number | 82032000 |
| EAN | 4028177930957 |
| ETIM 9 | EC000168 |

Features

| | |
|------------|----------|
| ETIM 8 | EC000168 |
| ECLASS 8.0 | 21043811 |