## Rittal – The System.

Faster – better – everywhere.






## PS 4157.000 U nut

State: 12/12/2025 (Source: rittal.com/ro-ro)



## PS 4157.000 - U nut

For mounting punched rails and punched sections without mounting flanges on angle brackets, mounting brackets and support brackets.



## **Features**

Model No.	PS 4157.000
Installation options	Punched rail 23 x 23 mm  Punched section without mounting flange, 23 x 73 mm  Punched section without mounting flange, 45 x 88 mm  Punched section with mounting flange, 23 x 73 mm
Note	For mounting punched rails and punched sections without mounting flanges on angle brackets, mounting brackets and support brackets, we recommend U nuts with M6 thread
Dimensions	Thread: M5
Thread	M5
Packs of	20 pc(s).
Net weight	0.34
Gross weight	0.36
Customs tariff number	73181692
EAN	4028177092822
ETIM 9	EC000096
ETIM 8	EC000096
ECLASS 8.0	23110804

© Rittal 2025