

Rittal – The System.

Faster – better – everywhere.



SZ 4174.000

Punched rail 23 x 23 mm

State: 07/07/2026 (Source: rittal.com/ro-ro)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SZ 4174.000 - Punched rail 23 x 23 mm for VX, TS, VX SE

For mounting on the horizontal and vertical enclosure sections via additional assembly components.



Features

Model No.	SZ 4174.000
Material	Sheet steel
Surface finish	Zinc-plated
Length	1.095 mm
Installation options	On the vertical enclosure section: Directly via support brackets TS, via adaptor rail for PS compatibility in conjunction with angle brackets, mounting brackets or support brackets PS On the horizontal enclosure section: Directly via angle brackets, mounting brackets or support brackets PS
To fit	Enclosure type: VX TS VX SE Suitable for width or height or depth: 1,200 mm
Packs of	6 pc(s).
Net weight	4,002 kg
Gross weight	4,202 kg
PCF per pack (cradle-to-gate)	21.3 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Customs tariff number	73269098

Features

ETIM 9	EC002620
ETIM 8	EC002620
ECLASS 8.0	27189234
Product description	SZ Punched rail 23 x 23 mm, for TS, SE, for WHD: 1200 mm, L: 1095 mm

Approvals

Explanations	PCF-declaration
--------------	-----------------