

Rittal – The System.

Faster – better – everywhere.



VX 5302.032

Slide rail, 2 U, static installation,
heavy duty

State: 10/02/2026 (Source: ittal.com/ro-ro)



ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

VX 5302.032 - Slide rail, 2 U, static installation, heavy duty for VX IT

For mounting between a front and rear pair of mounting angles for 482.6 mm (19") standard mounting angles and 482.6 mm (19") dynamic mounting angles in the VX IT.



Features

| | |
|----------------------|---|
| Model No. | VX 5302.032 |
| Product description | Side system punchings for mounting accessories and cooling components that expel to the side. |
| Benefits | Simply locate into the system punchings of the 482.6 mm (19") mounting brackets after adjusting the required 482.6 mm (19") distance between levels |
| Applications | For attachment between the front and rear 482.6 mm (19") mounting level To support heavy installed equipment |
| Material | Sheet steel |
| Surface finish | Zinc-plated |
| Supply includes | Assembly parts |
| Load capacity | 2000 N, static |
| Note | Effective contact surface 35 mm per side |
| Installation options | for 482.6 mm (19") mounting angles, standard: Distance between levels 520/545 mm for 482.6 mm (19") mounting angles, dynamic: Distance between levels 500/525 mm |

Features

| | |
|-----------------------|---------------|
| Packs of | 2 pc(s). |
| Net weight | 1.76 |
| Gross weight | 1.76 |
| Customs tariff number | 73269098 |
| EAN | 4028177952614 |
| E-Number Sweden | E7282592 |
| ETIM 9 | EC002620 |
| ECLASS 8.0 | 27189261 |
