

# Rittal – The System.

Faster – better – everywhere.



## VX\_IT 5302.109

## 482.6 mm (19") mounting angles, standard

State: 15/07/2025 (Source: [rittal.com/ro-ro](http://rittal.com/ro-ro))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# VX\_IT 5302.109 - 482.6 mm (19") mounting angles, standard for VX IT

Suitable for assembling a 482.6 mm (19") mounting level or for 482.6 mm (19") partial installation. The L-shaped design directly accommodates all commercially available installation kits for server installation kits for server systems, which are fastened directly to the 19" system punchings.

## Features

|                          |  |
|--------------------------|--|
| Model No.                | VX IT 5302.109   |
| Design                   | for VX IT 482.6 mm (19") mounting angles, standard   |
| Product description      | Suitable for assembling a 482.6 mm (19") mounting level or for 482.6 mm (19") partial installation. The L-shaped design directly accommodates all commercially available installation kits for server systems, which are fastened directly to the 482.6 mm (19") system punchings. |
| Benefits                 | Integral, bidirectional U labelling<br>Integral system punchings on a U pitch pattern on the front and sides, allows U-specific mounting of cable routing components for structured cabling  |
| Technical specifications | Side punchings, round and square, on a U pitch pattern<br>Potential equalisation within the mounting level and with the locating frame is achieved via the assembly components<br>482.6 mm (19") mounting hole including U centre fixing attachment to standard EIA 310 E          |
| Applications             | For mounting a 482.6 mm (19") mounting level within the VX IT rack system  |
| Material                 | Sheet steel, 2 mm  |
| Surface finish           | Primed   |
| Colour                   | RAL 9005   |
| Supply includes          | Assembly parts   |
| Mounting position        | rear   |

# Features

|                               |  |
|-------------------------------|--|
| Installation options          | Alternative installation widths from 21" – 24", depending on the mounting variant and rack dimensions selected   |
| Assembly instruction          | To be combined with cross-member, depth stays or mounting bracket for attachment<br>Use of the different mounting options depends on the relevant enclosure dimensions |
| To fit                        | Height: = 47 U   |
| Packs of                      | 2 pc(s).   |
| Net weight                    | 8.5  |
| Gross weight                  | 9.72   |
| PCF per pack (cradle-to-gate) | 37 kg CO2 eq (Cat B)   |
| Note on PCF category          | Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared   |
| Customs tariff number         | 73269098   |
| EAN                           | 4028177955479  |
| ETIM 9                        | EC002620   |
| ECLASS 8.0                    | 27189261   |