

Rittal – The System.

Faster – better – everywhere.



DK 5501.400

Slide rail, 2 U, static installation

State: 22/05/2026 (Source: rittal.com/ro-ro)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 5501.400 - Slide rail, 2 U, static installation for VX IT

For mounting between 482.6 mm (19") mounting angles.

Features

| | |
|-------------------------------|---|
| Model No. | DK 5501.400 |
| Product description | System punchings for mounting accessories and cooling active components. |
| Applications | For mounting on a 482.6 mm (19") mounting level |
| Material | Sheet steel |
| Surface finish | Zinc-plated |
| Supply includes | Assembly parts |
| Length | 150 mm |
| Installation options | for 482.6 mm (19") mounting angles, standard for 482.6 mm (19") mounting angles, dynamic |
| Load capacity | 300 N, static |
| Packs of | 2 pc(s). |
| Net weight | 0,62 kg |
| Gross weight | 0,703 kg |
| PCF per pack (cradle-to-gate) | 2.6 kg CO2 eq (Cat B) |
| Note on PCF category | Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared |
| Customs tariff number | 73269098 |
| ETIM 9 | EC002620 |
| ECLASS 8.0 | 27189261 |
| Product description | DK Slide rail, 2 U, D: 150 mm, 30 kg, static, For a 482.6 mm (19") attachment level, static installation, for 482.6 mm (19") system punchings |