

# Rittal – The System.

Faster – better – everywhere.



## SM 6450.070 TFT monitor

State: 22/05/2026 (Source: [rittal.com/ro-ro](http://rittal.com/ro-ro))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SM 6450.070 - TFT monitor

Installation variant for surfaces and command panels.

## Features

Model No.	SM 6450.070
Design	Touch, resistive, USB
Product description	Installation variant for surfaces and command panels.
Benefits	High-quality industrial design Reduced installation work thanks to integral front frame No additional ventilation required Very small installation depth (45 mm)
Material	Front frame: Aluminium
Surface finish	Powder-coated
Colour	RAL 7035
Supply includes	Seal Hex nuts (for installation in surfaces) VGA cable Threaded bolt M5, for rear mounting Touch variants additionally with integral connection cable and CD-ROM driver
Dimensions	Width: 430 mm Height: 343 mm
Interfaces	VGA (D-Sub HD 15-pole) DVI-D
Operating temperature range	0 °C...50 °C
Storage temperature range	-40 °C...85 °C
Display brightness	400 cd/m <sup>2</sup>
Contrast ratio	700 : 1
Diagonal	15"
Hours of operation	50.000 h

# Features

---

On Screen Display (OSD)	Operating buttons at the rear
Reading angle left/right	80 °
Resolution of display	1024 x 768 pixels
Note on Model No.	With VGA + DVI
Power consumption Pel	With DC: 15 W
H-Sync. (min./max.)	31.4 - 80 kHz
V-Sync. (min./max.)	60 - 75 Hz
Number of colours	16,2
Resolution of controller	VGA SVGA XGA
Packs of	1 pc(s).
Net weight	2 kg
Gross weight	2,1 kg
Customs tariff number	85286200
ETIM 9	EC001428
ECLASS 8.0	19200201
Product description	SM TFT monitor, 15", VGA, DVI-D

# Approvals

---

Explanations	Declaration of conformity
--------------	---------------------------