

**Rittal – The System.**

Faster – better – everywhere.



# DK 7030.087 CMC III cable clamp straps

State: 27/05/2026 (Source: [rittal.com/ro-ro](http://rittal.com/ro-ro))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# DK 7030.087 - CMC III cable clamp straps

For cable clamping and accommodation at the rear of the CMC III 482.6 mm (19") mounting unit.

## Features

|                                   |   |
|-----------------------------------|---|
| Model No.                         | DK 7030.087   |
| Product description               | For tool-free securing to the rear of the CMC III 482.6 mm (19") mounting unit 7030.088. Enables tidy cable routing behind the built-in CMC III devices and attachment of the cables for strain relief purposes. Cables can easily be laid in a loop to allow the built-in CMC III devices to be removed from the mounting unit without the need for tools. |
| Benefits                          | Cable run<br>Fire protection: Self-extinguishing to UL 94 HB  |
| Applications                      | Cable management  |
| Material                          | Plastic   |
| Colour                            | RAL 9005  |
| Supply includes                   | Assembly parts  |
| Length                            | 455 mm  |
| Dimensions                        | Width: 150 mm<br>Height: 50 mm<br>Length: 455 mm  |
| Operating temperature range       | 0 °C...55 °C  |
| Ambient humidity (non-condensing) | 5...95 %  |
| Packs of                          | 1 pc(s).  |
| Net weight                        | 0,4 kg  |
| Gross weight                      | 0,503 kg  |
| Customs tariff number             | 39269097  |
| ETIM 9                            | EC000322  |
| ECLASS 8.0                        | 27189253  |

# Features

---

## Product description

DK CMC III cable clamp straps, for tool-free attachment at the rear of the CMC III 19" mounting unit 7030.088. For cable routing at the rear of the CMC III components, RAL 9005