Rittal - The System.

Faster – better – everywhere.





DK 7401.000 Depth stays

State: 15/11/2025 (Source: rittal.com/ro-ro)



DK 7401.000 - Depth stays for Data Rack

For securing and stabilising two pairs of 482.6 mm (19") mounting angles in the Data Rack, the length is adjustable.

Features

| DK 7401.000 |
|---|
| For securing and stabilising two pairs of 482.6 mm (19") mounting angles in the Data Rack. The length of the depth stays is adjustable, and can accommodate the following spacings of mounting angles: 250, 300 and 350 mm. |
| Sheet steel |
| Spray-finished |
| RAL 7035 |
| Assembly parts |
| Installation depth for components: 482.6 mm Installation width for components: 19" |
| 2 pc(s). |
| 0.76 |
| 0.906 |
| 3.5 kg CO2 eq (Cat B) |
| Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared |
| 73269098 |
| 4028177129993 |
| E7282524 |
| EC002620 |
| 27189261 |
| |

© Rittal 2025

Tender text

Depth stays

For securing and stabilising two pairs of 482.6 mm (19") mounting levels in the data rack. The length of the depth stay can be adjusted and it enables a 50 mm pitch pattern to be set up for the mounting angles.

Material: Sheet steel Surface finish: RAL 7035

© Rittal 2025