

# Rittal – The System.

Faster – better – everywhere.



## DK 7824.282

## Sheet steel glazed door, vertically divided

State: 07/08/2025 (Source: [rittal.com/ro-ro](https://rittal.com/ro-ro))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# DK 7824.282 - Sheet steel glazed door, vertically divided for TS 8

To replace existing doors. Thanks to the minimal rotation radius of the individual doors, the distance between individual bayed enclosure suites may be reduced.

## Features

|                                     |   |
|-------------------------------------|---|
| Model No.                           | DK 7824.282   |
| Product description                 | With underlaid viewing panel, 4-point locking rod and comfort handle for profile half-cylinders with security lock 3524 E. The divided design allows room-optimised siting of the enclosures coupled with the best possible access, thanks to a reduced distance between the individual bayed enclosure suites. Max. door opening angle thanks to pre-integrated 180° hinges. |
| Material                            | Frame: Sheet steel<br>Viewing window: Single-pane safety glass, 3 mm  |
| Surface finish                      | Powder-coated   |
| Colour                              | RAL 7035  |
| Supply includes                     | Assembly parts  |
| Note                                | Height 2200 mm cannot be combined with swing frame 45 U.  |
| IP protection category to IEC 60529 | IP 55   |
| To fit                              | Enclosure type: TS 8<br>Width: 800 mm<br>Height: 2,200 mm   |
| Packs of                            | 1 pc(s).  |
| Net weight                          | 37.6  |
| Gross weight                        | 37.6  |
| EAN                                 | 4028177570931   |
| ECLASS 8.0                          | 27182204  |

# Tender text

Sheet steel glazed door, vertically divided for TS  
With underlaid viewing panel, 4-point locking rod  
and comfort handle for semi-cylinder with security  
lock 3524 E. Max. door opening angle 180°.

## Note:

Cannot be combined with swing frame 45 U.

Material: Sheet steel, viewing window  
toughened safety glass 4 mm

Colour: RAL 7035

For enclosures (W x H): 800 x 2200 mm