

# Rittal – The System.

Faster – better – everywhere.



## DK 7824.490

## All-glass door, vertically divided

State: 12/07/2025 (Source: [rittal.com/ro-ro](https://www.rittal.com/ro-ro))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# DK 7824.490 - All-glass door, vertically divided for DK-TS

To replace existing doors. Thanks to the minimal rotation radius of the individual doors, the distance between individual bayed enclosure suites may be reduced.

## Features

Model No.	DK 7824.490
Product description	With 180° hinges and locking rod including comfort handle with security lock no. 3524 E. Thanks to the minimal rotation radius of the individual doors, the distance between individual bayed enclosure suites may be reduced.
Material	Frame elements: Aluminium Viewing window: Single-pane safety glass, 5 mm
Colour	Frame: RAL 7035 Viewing windows: Tinted
Supply includes	Assembly parts
Note	Not to be used in conjunction with a swing frame
To fit	Enclosure type: DK-TS Width: 800 mm Height: 2,000 mm
Packs of	1 pc(s).
Net weight	24.951
Gross weight	26.264
Customs tariff number	76169990
EAN	4028177442467
ECLASS 8.0	27182204

# Tender text

Vertically divided all-glass door, including 180° hinges

180° hinges and locking rod including comfort handle with 3124 E security lock.

Material: sheet steel, spray finished in RAL 7035; 5 mm single-pane safety glass, surrounding frame made from aluminium; tinted, parsol grey safety glass

Enclosure W x D: 800 mm x 2000 mm