


**Rittal – The System.**

Faster – better – everywhere.



**TS 7826.665**

**Roof plate for cable entry, two-piece**

State: 09/02/2026 (Source: [rittal.com/ro-ro](http://rittal.com/ro-ro))



ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

# TS 7826.665 - Roof plate for cable entry, two-piece for VX, VX IT, TS, TS IT

The two-piece design allows easy retro-fitting, by simply removing the front part of the plate for retrospective cable entry.



## Features

|                       |   |
|-----------------------|---|
| Model No.             | TS 7826.665   |
| Product description   | In exchange for the standard roof. Equipped with a sliding angular bracket in the rear section. Rubber cable clamp strip on both sides for attaching cable bundles and bunched cables. Due to the symmetrical design of the frame, side cable entry can also be achieved by rotating the roof plate. The two-piece design allows convenient retrofitting. |
| Material              | Sheet steel   |
| Colour                | RAL 7035  |
| To fit                | Width: 600 mm<br>Depth: 600 mm  |
| Packs of              | 1 pc(s).  |
| Net weight            | 5.136   |
| Gross weight          | 5.38  |
| Customs tariff number | 94039910  |
| EAN                   | 4028177390225   |
| E-Number Sweden       | E7239737  |
| ETIM 9                | EC000744  |

# Features

---

ECLASS 8.0

27182405

## Tender text

Roof plate for cable entry, two-piece for TS, TS IT

Material: Sheet steel, spray-finished in RAL 7035

Dimensions (W x D): 600 mm x 600 mm