Rittal - The System.

Faster – better – everywhere.





TS 7826.685 Roof plate for cable entry, two-piece

State: 07/11/2025 (Source: rittal.com/ro-ro)



TS 7826.685 - Roof plate for cable entry, two-piece for VX, VX IT, TS, TS IT

The two-piece design allows easy retro-fitting, by simply removing the front part of the plate for retrospective cable entry.



Features

Model No.	TS 7826.685
Product description	In exchange for the standard roof. Equipped with a sliding angular bracket in the rear section. Rubber cable clamp strip on both sides for attaching cable bundles and bunched cables. Due to the symmetrical design of the frame, side cable entry can also be achieved by rotating the roof plate. The two-piece design allows convenient retrofitting.
Material	Sheet steel
Colour	RAL 7035
To fit	Width: 600 mm Depth: 800 mm
Packs of	1 pc(s).
Net weight	6.745
Gross weight	7.1
Customs tariff number	94039910
EAN	4028177345331
E-Number Sweden	E7239738
ETIM 9	EC000744

© Rittal 2025

Features

ECLASS 8.0

27182405

Tender text

Cable entry roof plate for TS, TS IT $W \times D = 600 \times 800 \text{ mm}$, two-piece

Material: Sheet steel, spray finished in RAL 7035

Dimensions (W x D): 600 mm x 800 mm

© Rittal 2025 3