



Rittal – The System.

Faster – better – everywhere.



CP 7994.350 Pedestal, open

State: 15/12/2025 (Source: [rittal.com/ro-ro](https://www.rittal.com/ro-ro))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



CP 7994.350 - Pedestal, open Mercedes-Benz Integra Standard

For fixed or rotating attachment of HVO command panels.

Features

Model No.	CP 7994.350
Design	rigid
Product description	Pedestal for fixed or rotating attachment of HVO command panels.
Material	Steel
Surface finish	Spray-finished
Colour	RAL 7035
Supply includes	Pedestal tube extrusion 86 x 73 mm, welded vertically onto the base plate Rear pedestal tube with a vertical opening across the entire height to accommodate cables, sealed with cover section no. 30007784 (from K-Profile). Rear pedestal tube – bracket for cable clamping welded into the vertical opening, distance from top edge of base plate to bottom edge of bracket: 243.5 mm Earthing bolt M8 x 20 mm is welded into the lower section of the vertical opening. Distance from top edge of base plate to centre of earthing bolt: 40.0 mm Earthing bolt M5 x 15 mm is welded into the upper section of the vertical opening. Distance from bottom edge of head plate to centre of earthing bolt: 60.0 mm Both earthing bolts are labelled with earthing stickers
Width base plate	400 mm
Height base plate	10 mm
Depth base plate	400 mm
Height pedestal tube	1.169 mm
Dimensions	Height: 1,213 mm

Features

Packs of	1 pc(s).
Net weight	24
Gross weight	24.5
Customs tariff number	73269098