Rittal - The System.

Faster – better – everywhere.





TS 8128.235

Side panel, screw-fastened, sheet steel

State: 04/11/2025 (Source: rittal.com/ro-ro)



TS 8128.235 - Side panel, screw-fastened, sheet steel for TS, TS IT

Side panels, screw-fastened, sheet steel, for TS.

Features

Model No.	TS 8128.235	
Benefits	Automatic potential equalisation and higher EMC protection due to enclosure panel holders with earthing insert Easy positioning with the location aid Earthing bolt with contact surface	
Material	Sheet steel, 1.5 mm	
Surface finish	Dipcoat-primed, powder-coated on the outside	
Colour	RAL 7035	
Supply includes	Assembly parts	
Note	Enclosure panel holders may optionally be fitted from the inside o outside of the enclosure Area available for population: External dimension – 100 mm	
To fit	Enclosure type: TS TS IT Height: 2,200 mm Depth: 800 mm	
IP protection category to IEC 60 529	IP 55	
Basic material	Sheet steel	
Packs of	2 pc(s).	
Net weight	43	
Gross weight	44	
Customs tariff number	94039910	
EAN	4028177237223	

© Rittal 2025

Features

E-Number Sweden	E7238412	
ETIM 9	EC002524	
ECLASS 8.0	27182101	

Tender text

Side panel, screw-fastened, for TS
Easy positioning on the frame with the location aid.
The enclosure panel holders with earthing insert
ensure automatic potential equalisation and higher
EMC protection.

They may optionally be fitted from the inside or outside of the enclosure.

When using TS side panel hinges an opening angle of 180° is possible.

Material: 1.5 mm sheet steel

Area available for population: External dimension 100 mm

Protection category: IP 55

Surface finish:
Dipcoat-primed,
powder-coated in textured RAL 7035
on the outside

For enclosure dimensions: H: 2200 mm D: 800 mm

© Rittal 2025 3