Rittal – The System.

Faster – better – everywhere.





TS 8184.235

Side panel, screw-fastened, sheet steel

State: 25/11/2025 (Source: rittal.com/ro-ro)



TS 8184.235 - Side panel, screw-fastened, sheet steel for TS, TS IT

Side panels, screw-fastened, sheet steel, for TS.

Features

Model No.	TS 8184.235
Benefits	Automatic potential equalisation and higher EMC protection due to
	enclosure panel holders with earthing insert
	Easy positioning with the location aid
	Earthing bolt with contact surface
Material	Sheet steel, 1.5 mm
Surface finish	Dipcoat-primed, powder-coated on the outside
Colour	RAL 7035
Supply includes	Assembly parts
Note	Enclosure panel holders may optionally be fitted from the inside or
	outside of the enclosure
	Area available for population: External dimension – 100 mm
To fit	Enclosure type: TS
	TS IT
	Height: 1,800 mm
	Depth: 400 mm
IP protection category to IEC 60 529	IP 55
Basic material	Sheet steel
Packs of	2 pc(s).
Net weight	16.6
Gross weight	17.8
Customs tariff number	94039910
	4028177205215

© Rittal 2025

Features

ETIM 9	EC002524
ECLASS 8.0	27182101

Approvals

Explanations Declaration of conformity UK

© Rittal 2025 3