

Rittal – The System.

Faster – better – everywhere.



TS 8612.260

TS punched rail 18 x 38 mm

State: 28/08/2025 (Source: rittal.com/ro-ro)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE


SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



TS 8612.260 - TS punched rail 18 x 38 mm

Installation on the vertical TS enclosure section on the outer mounting level, on the horizontal TS enclosure section and on the base configuration rail for CM.



Features

Model No.	TS 8612.260
Product description	Simply locate and secure with a screw. The location system makes assembly and dismantling easier. It only needs to be secured on one side, but may be secured on both sides if required.
Material	Sheet steel
Supply includes	Assembly screws
Installation options	On the vertical TS, VX SE enclosure section on the outer mounting level On the horizontal TS, VX SE enclosure section On base configuration rail for TP
Note	In enclosures with a mounting plate, 2 punched rails are already included with the supply.
To fit	To fit width/depth: 600 mm
Packs of	4 pc(s).
Net weight	2.5
Gross weight	2.669
Customs tariff number	73269098
EAN	4028177213104
ETIM 9	EC002625

Features

ECLASS 8.0

27189234