Rittal - The System.

Faster – better – everywhere.





TS 8612.550

TS punched section with mounting flange, 23 x 73 mm

State: 04/11/2025 (Source: rittal.com/ro-ro)



TS 8612.550 - TS punched section with mounting flange, 23 x 73 mm

The alternative to the TS punched section with mounting flange 17×73 mm, with punchings for captive nuts/threaded blocks instead of the slotted holes top and bottom. Simply locate and secure.





Features

Model No.	TS 8612.550
Product description	The alternative to the TS punched section with mounting flange 17 x 73 mm, with punchings for captive nuts/threaded blocks instead of the slotted holes top and bottom. Simply locate and secure.
Material	Sheet steel
Surface finish	Zinc-plated
Supply includes	Assembly screws
Installation options	On the vertical TS, VX SE enclosure section
To fit	Enclosure type: the inner mounting level To fit width/depth: 500 mm
Packs of	4 pc(s).
Net weight	2.084
Gross weight	2.283
Customs tariff number	73269098
EAN	4028177236264
ETIM 9	EC002625

© Rittal 2025 2

Features

ECLASS 8.0

27189234

© Rittal 2025 3