

Rittal – The System.

Faster – better – everywhere.



TS 8612.650

TS punched sections without mounting flanges, 45 x 88 mm

State: 12/04/2026 (Source: rittal.com/ro-ro)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



TS 8612.650 - TS punched sections without mounting flanges, 45 x 88 mm

Heavy top-mounted equipment mounted directly on the internal surfaces (e.g. roof) is supported. Mounted on the side or rear, the enclosure can then be screw-fastened securely to the machine.



Features

Model No.	TS 8612.650
Design	for the inner mounting level
Product description	Heavy top-mounted equipment mounted directly on the internal surfaces (e.g. roof) is supported. Mounted on the side or rear, the enclosure can then be screw-fastened securely to the machine. The twin profile with 11 rows of holes offers numerous additional opportunities for interior installation.
Material	Sheet steel
Surface finish	Zinc-plated
Supply includes	Assembly parts
Installation options	On the vertical and horizontal TS, VX SE enclosure section
To fit	Enclosure type: the inner mounting level Width/depth: 500 mm
Packs of	2 pc(s).
Net weight	2,6 kg
Gross weight	2,611 kg
Customs tariff number	73269098

Features

ETIM 9	EC002625
ECLASS 8.0	27189234
Product description	TS TS punched section without mounting flange, 45 x 88 mm, for inner mounting level: for WD: 500 mm
