

Rittal – The System.

Faster – better – everywhere.



TS 8800.570 Cable duct

State: 22/05/2026 (Source: rittal.com/ro-ro)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



TS 8800.570 - Cable duct for vertical TS section

For mounting on the vertical enclosure section, on two bayed enclosure sections in the vicinity of baying.



Features

| | |
|-----------------|--|
| Model No. | TS 8800.570 |
| Design | Width 50 mm, for assembly on one vertical enclosure section in the area of the side panel. |
| Benefits | <p>The cable duct fastening points are co-ordinated with the TS system hole pattern. This eliminates time-consuming drilling work that would be necessary with DIN ducts.</p> <p>The nominal break points of the bars are also designed for combination with the cable ducts for mounting plates.</p> <p>A further nominal break at the mounting plate height allows direct entry to the cable duct.</p> |
| Material | Hard PVC Flame-resistant, self-extinguishing |
| Colour | Similar to RAL 7030 |
| Supply includes | Cable duct with cover |
| Bar width | 5,5 mm |
| Slot width | 4,5 mm |
| Note | Can be shortened for other enclosure sizes. |

Features

| | |
|-----------------------------|---|
| Dimensions | Width: 50 mm Height: 1,600 mm Depth: 80 mm |
| To fit | Enclosure type: TS VX SE PC IW Height: ≤ 1,800 mm |
| Operating temperature range | 60 °C |
| Packs of | 8 pc(s). |
| Net weight | 8,968 kg |
| Gross weight | 9,44 kg |
| Customs tariff number | 39259020 |
| ETIM 9 | EC000012 |
| ECLASS 8.0 | 27400703 |
| Product description | TS Cable duct for vertical TS section, WHD: 50x1600x80 mm |

Approvals

| | |
|--------------|---|
| Explanations | Declaration of conformity Declaration of conformity UK |
|--------------|---|