

Rittal – The System.

Faster – better – everywhere.



SV 9340.000 Busbar support

State: 13/05/2026 (Source: rittal.com/ro-ro)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9340.000 - Busbar support for flat copper busbars

For flat copper bars up to 800 A.

Features

Model No.	SV 9340.000
Material	Polyamide Fire protection corresponding to UL 94-V0
Colour	RAL 7035
Rated operating voltage	1000 V, 3~
Note on Model No.	If 12 x 5/10 mm busbars are used, spacer 9340.090 is additionally required
Number of poles	3-pole
To fit Model No.	9580000 3581000 3582000 3583000 3584000 3580100 3581100 3585005 3586005
Internal attachment	Yes
Centre-to-centre spacing of busbars	60 mm
To fit busbars	12 x 5 - 30 x 10
Packs of	4 pc(s).
Net weight	0,724 kg
Gross weight	0,732 kg
Customs tariff number	85469010
ETIM 9	EC001166

Features

ECLASS 8.0	27400607
------------	----------

Product description	SV Busbar support, 3-pole, 60 mm bar centre distance, for busbar WH: 12x5-30x10 mm
---------------------	---

Approvals

Approvals	ABS DNV Lloyds Register
-----------	-------------------------------

Explanations	Declaration of conformity Declaration of conformity UK
--------------	---

Tender text

RiLine60 busbar support, 3-pole
Busbar support with internal attachment, 3-pole
Technical specifications
Bar centre distance: 60 mm
Busbars E-Cu: 12 x 5/10, 15 x 5 to 30 x 10 mm
Construction width: 20 mm
Length: 190 mm
System:
Rittal RiLine60