

# Rittal – The System.

Faster – better – everywhere.



## SV 9617.000

## Mini-PLS component adaptor

State: 10/06/2026 (Source: [rittal.com/ro-ro](http://rittal.com/ro-ro))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 9617.000 - Mini-PLS component adaptor

Maximum rated current from 12 A to 100 A.

## Features

|                              |   |
|------------------------------|---|
| Model No.                    | SV 9617.000   |
| Material                     | Polyamide<br>Fire protection corresponding to UL 94-V0  |
| Colour                       | RAL 7035  |
| Connection cables (AWG)      | AWG 10  |
| Rated operating voltage      | 690 V, 3~   |
| Rated current max.           | 40 A  |
| Dimensions                   | Width: 54 mm<br>Height: 160 mm  |
| Support rails Qty/height     | 1 / 15 mm   |
| To fit manufacturer (model)  | ABB<br>Eaton<br>MS450 max. 40 A<br>PKZM4 max. 40 A  |
| Packs of                     | 1 pc(s).  |
| Net weight                   | 0,33 kg   |
| Gross weight                 | 0,374 kg  |
| Copper weight (kg per piece) | 0,046   |
| Customs tariff number        | 85369095  |
| ETIM 9                       | EC001531  |
| ECLASS 8.0                   | 27370304  |
| Product description          | SV Mini-PLS component adaptor, 40 A, 690 V, 3-pole, connection cable AWG 10, WH: 54x160 mm, support rail H: 15 mm |

# Approvals

---

|              |   |
|--------------|---|
| Approvals    | UR + C-UR (recognized)                                    |
| Explanations | Declaration of conformity<br>Declaration of conformity UK |

---