## Rittal – The System.

Faster - better - everywhere.





# SV 9635.320 Component adaptor

State: 02/11/2025 (Source: rittal.com/ro-ro)



# SV 9635.320 - Component adaptor 3-pole

For assembly of switchgear and protective gear.

#### **Features**

| Model No.                    | SV 9635.320  |
|------------------------------|--|
| Design                       | Basic  |
| Function principle           | For mechanical attachment and direct contacting of electrical equipment on the board |
| Material                     | Polyamide Fire protection corresponding to UL 94                                     |
| Colour                       | RAL 7035   |
| Note                         | The technical data may vary for UL applications                                      |
| Rated current max.           | 32 A   |
| Rated operating voltage      | 600 V (DC), 3~<br>690 V (AC), 3~   |
| Number of poles              | 3-pole   |
| Electrical ratings UL        | Rated operating voltage (max.) UL: 600 V AC  |
| Connection cables (AWG)      | AWG 10   |
| Length of connection cable   | 100 mm   |
| Support rails Qty/height     | 1 / 10 mm  |
| Support rail type            | static   |
| Dimensions                   | Width: 45 mm<br>Height: 160 mm<br>Depth: 34.5 mm                                     |
| Packs of                     | 4 pc(s).   |
| Net weight                   | 0.44   |
| Gross weight                 | 0.513  |
| Copper weight (kg per piece) | 0.044  |

© Rittal 2025

### Features

| Customs tariff number | 85369095      |
|-----------------------|---------------|
| EAN                   | 4028177817364 |
| ETIM 9                | EC001531      |
| ECLASS 8.0            | 27370304      |

## **Approvals**

| Approvals    | UL + C-UL (listed)           |
|--------------|------------------------------|
| Explanations | Declaration of conformity    |
|              | Declaration of conformity UK |

© Rittal 2025 3