

# Rittal – The System.

Faster – better – everywhere.



## SV 9635.372 Component adaptor

State: 28/08/2025 (Source: [rittal.com/ro-ro](https://www.rittal.com/ro-ro))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 9635.372 - Component adaptor 1-pole

For assembly of switchgear and protective gear.

## Features

|                              |  |
|------------------------------|--|
| Model No.                    | SV 9635.372  |
| Design                       | L2   |
| Function principle           | For mechanical attachment and direct contacting of electrical equipment on the board   |
| Material                     | Polyamide<br>Fire protection corresponding to UL 94  |
| Colour                       | RAL 7035   |
| Note                         | Different adaptor versions are required depending on the preferred phase connection<br>The technical data may vary for UL applications |
| Rated current max.           | 16 A   |
| Rated operating voltage      | 690 V (AC), 1~   |
| Number of poles              | Single-pole  |
| Connection cables (AWG)      | AWG 14   |
| Length of connection cable   | 100 mm   |
| Support rails Qty/height     | 1 / 10 mm  |
| Support rail type            | static   |
| Dimensions                   | Width: 18 mm<br>Height: 160 mm<br>Depth: 35 mm   |
| Packs of                     | 6 pc(s).   |
| Net weight                   | 0.33   |
| Gross weight                 | 0.373  |
| Copper weight (kg per piece) | 0.008  |

# Features

|                       |               |
|-----------------------|---------------|
| Customs tariff number | 85369095      |
| EAN                   | 4028177934580 |
| ETIM 9                | EC001531      |
| ECLASS 8.0            | 27370304      |

# Approvals

|              |   |
|--------------|---|
| Approvals    | UL + C-UL (listed)  |
| Explanations | Declaration of conformity<br>Declaration of conformity UK |