

Rittal – The System.

Faster – better – everywhere.



SV 9677.905

Connection adaptor

State: 08/02/2026 (Source: rittal.com/ro-ro)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9677.905 - Connection adaptor

For the connection of round conductors. For bar systems with 185 mm centre-to-centre spacing.

Features

Model No.	SV 9677.905
Material	Chassis: Fibreglass-reinforced polyester Fire protection corresponding to UL 94-V0
Colour	RAL 7035
Supply includes	Contact hazard protection cover plate
For bar systems with centre-to-centre spacing	185 mm
Cable outlet	Top/bottom
Type of electrical connection	Screw M12
Number of poles	3-pole
Rated current max.	1.400 A
Rated operating voltage	690 V, 3~
Note	When using components on busbars with contact hazard protection cover, the contact terminal must be used
Dimensions	Width: 100 mm Height: 960 mm
Connection of round conductors	6 - 300 mm ²
To fit busbars	Height: 10 mm
Packs of	1 pc(s).
Net weight	11
Gross weight	11.5
Copper weight (kg per piece)	4.41
Customs tariff number	85369010
EAN	4028177705296

Features

ETIM 9 EC001531

ECLASS 8.0 27370304

Approvals

Explanations Declaration of conformity
Declaration of conformity UK