

# Rittal – The System.

Faster – better – everywhere.



## VX 1182.096

## VX IT Open

State: 05/05/2026 (Source: [rittal.com/rs-sr](http://rittal.com/rs-sr))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# VX 1182.096 - VX IT Open

VX IT standard version, without front and rear door. Usable either as an open 482.6 mm (19") frame in a secure environment or as the basis for fast configurations in the Rittal RiPanel configuration system using existing accessories (such as doors and side panels) from the Rittal modular range.



## Features

|                |  |
|----------------|--|
| Model No.      | VX 1182.096  |
| Design         | VX enclosure frame with roof plate<br>without front and rear door<br>Vented<br>without side panels |
| Surface finish | Enclosure frame: Dipcoat-primed<br>Interior installation: Spray-finished                           |
| General colour | RAL 7035   |
| Colour         | Enclosure frame and roof: RAL 7035<br>Interior installation: RAL 9005                              |

# Features

|   |  |
|---|--|
| Supply includes   | Enclosure frame<br>Mounting angles, 482.6 mm (19")<br>Spacers, height 50 mm, to raise a cover plate above the fan cut-out in the roof plate, for passive cooling (supplied loose). Not required for variants without a cut-out.<br>12 x 482.6 mm (19") fastener, 1 U, conductive (supplied loose)<br>25 multi-tooth screws, conductive (supplied loose)<br>IPPC pallet<br>Roof plate, multi-piece, with side cable entry in the depth, double-sided, prepared for fan mounting plate |
| Dimensions  | Width: 800 mm<br>Height: 2,000 mm<br>Depth: 800 mm   |
| Units   | 42 U   |
| Free mounting space to the 482.6 mm (19") level, front/rear | 150 mm / 130 mm  |
| Distance between levels as delivered                        | 520 mm   |
| 482.6 mm (19") attachment                                   | on the cross-member, screw-fastened at the top and bottom  |
| Design  | Standard   |
| Roof design   | multi-piece, with side cable entry in the depth, double-sided, prepared for fan mounting plate   |
| Mounting angle design                                       | 482.6 mm (19") mounting angles, standard in the VX IT  |
| Base design   | Open   |
| 482.6 mm (19") level(s) version                             | front and rear   |
| Load capacity   | 8.000 N  |
| Max. load capacity (static) per enclosure to UL 2416        | 8.000 N  |
| Basic material  | Sheet steel  |
| Packs of  | 1 pc(s).   |
| Net weight  | 52,9 kg  |
| Gross weight  | 66,4 kg  |

# Features

---

|                       |   |
|-----------------------|---|
| Customs tariff number | 94032080  |
| ETIM 9                | EC002499  |
| ETIM 8                | EC002499  |
| ECLASS 8.0            | 27180207  |
| Product description   | VX IT Open, 482.6 mm (19") mounting angles screw-fastened to depth cross-member at the top and bottom, WHD: 800x2000x800 mm, RAL 7035 |

# Approvals

---

|              |   |
|--------------|---|
| Explanations | Manufacturer's declaration<br>Declaration of conformity |
|--------------|---|