

Rittal – The System.

Faster – better – everywhere.



KX 1561.000 Terminal box KX

State: 22/06/2026 (Source: rittal.com/rs-sr)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



KX 1561.000 - Terminal box KX Stainless steel

The stainless steel terminal box KX delivers maximum data quality and consistency of engineering while ensuring flexibility and reliability across a wide range of applications.



Features

| | |
|-----------------------------------|--|
| Model No. | KX 1561.000 |
| Product description | The stainless steel terminal box KX delivers maximum data quality and consistency of engineering while ensuring flexibility and reliability across a wide range of applications. |
| Material | Enclosure: Stainless steel 1.4301 (AISI 304) Cover: Stainless steel 1.4301 (AISI 304), all-round foamed-in PU seal |
| Surface finish | Enclosure and cover: Brushed, grain 180 |
| Supply includes | Enclosure with cover Quick-release fastener including plastic bushes |
| Protection category NEMA | NEMA 1 NEMA 3R NEMA 3RX NEMA 4 NEMA 4X NEMA 12 |
| Protection category to IEC 60 529 | IP 66 |
| Type rating to UL 50E | Type 1 Type 3R Type 3RX Type 4 Type 4X Type 12 |

Features

| | |
|--------------------------------|---|
| Dimensions | Width: 300 mm Height: 150 mm Depth: 80 mm |
| Material thickness - cover | 1,25 mm |
| Material thickness - enclosure | 1,25 mm |
| Lock | Number of locks: 4 |
| Basic material | Stainless steel 1.4301 (AISI 304) |
| Packs of | 1 pc(s). |
| Net weight | 1,868 kg |
| Gross weight | 1,971 kg |
| PCF per pack (cradle-to-gate) | 7.86 |
| Customs tariff number | 84879059 |
| ETIM 9 | EC000261 |
| ETIM 8 | EC000261 |
| ECLASS 8.0 | 27180101 |
| Product description | KX Terminal box, WHD: 300x150x80 mm, stainless steel 1.4301, without mounting plate, with cover, with quick-release fasteners |

Approvals

| | |
|--------------|--|
| Approvals | Bureau Veritas DNV Lloyds Register UL + C-UL (listed) |
| Explanations | Declaration of conformity PCF-declaration |

Tender text

Enclosure (terminal box, stainless steel)

Enclosure with cover:

Stable stainless steel design,
body folded from a single piece and welded,
with protection channel all-round cover opening,
Solid rear panel with knockouts,
cover with foamed-in PU seal,
with PE conductor connection in the enclosure,
earthing in the cover via bolt,
for quick and easy earthing,
with quick-release fastener.

QR code:

QR code printed on body, cover and rating plate
for clear identification and easy retrieval of relevant
product information and documentation,
and for clear traceability of the individual parts.

Accessories: Cover hinge,
mounting plate, top hat rail, wall mounting bracket,
mounting claw for second mounting level.

Material:

Enclosure, cover: Stainless steel 1.4301 (AISI 304)

Surface finish: Brushed, grain size 400

Protection category to IEC 60 529: IP 66

Protection category to UL 508A: Type 4X

Dimensions (W x H x D): 300x150x80 mm