

Rittal – The System.

Faster – better – everywhere.



SZ 1581.200 Metal gland plate

State: 07/05/2026 (Source: rittal.com/rs-sr)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SZ 1581.200 - Metal gland plate with metric knockouts

Simply knock out the holes for the cable glands using a screwdriver, IP 66 when mounting in the usual position at the bottom.

Features

Model No.	SZ 1581.200
Product description	Simply knock out the holes for the cable glands using a screwdriver.
Material	Sheet steel
Colour	RAL 7035
Note	The allocation of gland plate sizes is indicated on the relevant enclosures
No. of metric knockouts	12 x M20
Dimensions	Width: 220 mm Depth: 90 mm
To fit	Enclosure type: KX
Protection category to IEC 60 529	IP 55 if installed correctly
Type rating to UL 50E	Type 1 Type 12K
Packs of	1 pc(s).
Net weight	0,23 kg
Gross weight	0,24 kg
PCF per pack (cradle-to-gate)	1.2 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Customs tariff number	73079100
ETIM 9	EC000211
ETIM 8	EC000211
ECLASS 8.0	27142421

Features

Product description	KX Metal gland plate, with metric knockouts, for cable diameter M20
---------------------	---

Approvals

Approvals	UL + C-UL - FTTA
-----------	------------------