

Rittal – The System.

Faster – better – everywhere.



HD 2410.001 Cable gland HD

State: 21/06/2026 (Source: rittal.com/rs-sr)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



HD 2410.001 - Cable gland HD

More compact design and the lock nut is included with the supply.



Features

| | |
|-----------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Model No. | HD 2410.001 |
| Design | Standard |
| Benefits | Smooth, solid exterior surfaces effectively prevent the depositing of harmful micro-organisms. Much easier, and therefore cheaper to clean compared with conventional cable glands. |
| Applications | Manufacturer Clean room technology (e.g. pharmaceuticals) Biotechnology Chemical industry |
| Material | Nut: Stainless steel 1.4305 (AISI 303) Seal: EPDM, compliant with FDA 21 CFR 177.2600 |
| Supply includes | Lock nut |
| Dimensions | Thread: M12 x 1.5 |
| For cable diameters | 3 - 6.5 mm |
| Operating temperature range | -20 °C...100 °C |

Features

| | |
|-------------------------------------|------------------------------------------------------------------------------------------------|
| IP protection category to IEC 60529 | IP69 / IPX8 (5 bar, 30 min) |
| Packs of | 5 pc(s). |
| Net weight | 0,095 kg |
| Gross weight | 0,134 kg |
| Customs tariff number | 73072980 |
| ETIM 9 | EC000441 |
| ETIM 8 | EC000441 |
| ECLASS 8.0 | 27149109 |
| Product description | HD Cable gland, stainless steel 1.4305, size: M12x1,5, for cables Ø 3-6.5 mm, Standard version |

Approvals

| | |
|-----------|-------------------------------|
| Approvals | UR + C-UR (recognized) VDE |
|-----------|-------------------------------|