

# Rittal – The System.

Faster – better – everywhere.



## FT 2796.000 Acrylic glazed cover

State: 13/05/2026 (Source: [rittal.com/rs-sr](http://rittal.com/rs-sr))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# FT 2796.000 - Acrylic glazed cover

For the protection of display and control components in standard 482.6 mm (19") or metric sizes.

## Features

Model No.	FT 2796.000
Design	482.6 mm (19")
Product description	With security lock, lock no. 3524 E.
Material	Frame: Extruded aluminium sections with die-cast corner pieces Glass panel: Smoked acrylic
Supply includes	Hinges and assembly parts. Lock insert no. 3524 E
Protection category to IEC 60 529	IP 54
Dimensions	Width: 534 mm Height: 425 mm Depth: 47.5 mm
Visible area	Viewing window width: 494 mm Viewing window height: 404.5 mm
Build depth for components (max.)	43 mm
Installation dimensions	Installation depth for components: 482.6 mm Installation width for components: 19"
Packs of	1 pc(s).
Net weight	2,475 kg
Gross weight	2,675 kg
Customs tariff number	39205100
ETIM 9	EC002527
ETIM 8	EC002527
ECLASS 8.0	27182301
Product description	FT Acrylic glazed cover, 482.6 mm (19"), WHD: 534x425x47,5 mm