

Rittal – The System.

Faster – better – everywhere.



AX 2820.102

Base/plinth corner piece with base/
plinth trim panels, front and rear,
200 mm

State: 23/05/2026 (Source: rittal.com/rs-sr)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AX 2820.102 - Base/plinth corner piece with base/plinth trim panels, front and rear, 200 mm for AX

Base/plinth corner piece with large opening for optimum access to the screw-fastening point, may be concealed with a plastic corner cover.

Features

| | |
|-----------------------|---|
| Model No. | AX 2820.102 |
| Product description | Base/plinth corner piece with large opening for optimum access to the screw-fastening point, may be concealed with a plastic corner cover. |
| Material | Base/plinth corner piece: Sheet steel Base/plinth trim panel front/rear: Sheet steel Corner cover: Plastic |
| Colour | RAL 9005 |
| Supply includes | 4 base/plinth corner pieces, 200 mm high 4 corner covers 1 base/plinth trim panel, front/rear, 200 mm high 2 base/plinth trim panels, front/rear, 100 mm high Assembly parts |
| Note | Base/plinth elements are required at the side to finish off a base/plinth unit Components from the 1st generation base/plinth system cannot be combined with components from the 2nd generation base/plinth system |
| Dimensions | Height: 200 mm |
| To fit | Enclosure type: AX Width: = 1,000 mm |
| Type rating to UL 50E | Type 1 Type 3R Type 4 Type 12 |
| Packs of | 2 pc(s). |

Features

| | |
|-----------------------|--|
| Net weight | 9,8 kg |
| Gross weight | 10,8 kg |
| Customs tariff number | 94039910 |
| ETIM 9 | EC000721 |
| ETIM 8 | EC000721 |
| ECLASS 8.0 | 27182003 |
| Product description | AX Base/plinth corner pieces with base/plinth trim panels, front and rear, H: 200 mm, for W: 1000 mm |

Approvals

| | |
|-----------|------------------|
| Approvals | UL + C-UL - FTTA |
|-----------|------------------|