

Rittal – The System.

Faster – better – everywhere.



SK 3124.010 Line reactor

State: 21/05/2026 (Source: rittal.com/rs-sr)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SK 3124.010 - Line reactor Wall-mounted cooling unit Blue e+ Dynamic

Line reactor for complying with EMC requirements to DNV-CG-0339 Class A.

Features

Model No.	SK 3124.010
Packs of	1 pc(s).
To fit Model No.	3184.837 / 3484.837 3185.837 / 3485.837 3186.937 / 3486.937 3187.937 / 3487.937
Dimensions	Width: 40 mm Height: 44 mm Length: 76 mm
Operating temperature range	0 °C...85 °C
Rated operating voltage	230 V, 1~, 50 Hz/60 Hz
IP protection category to IEC 60529	IP 00
Net weight	0,3 kg
Gross weight	0,382 kg
Customs tariff number	85059090
Product description	SK line reactor, for Blue e+ Dynamic wall-mounted cooling unit, 230 V, 1~, 50/60 Hz