

**Rittal – The System.**

Faster – better – everywhere.



**SK 3148.007**

**Roof-mounted fan, roof vent**

State: 31/05/2026 (Source: [rittal.com/rs-sr](http://rittal.com/rs-sr))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SK 3148.007 - Roof-mounted fan, roof vent

May be installed in any sufficiently large roof surface, air throughput 360 m<sup>3</sup>/h.

## Features

Model No.	SK 3148.007
Design	without fan motor
Product modification	Mounting cut-outs are not compatible. If reusing the roof plate, adaptor frame 5050.700 is required.
Material	Sheet steel, spray-finished
Colour	RAL 7035
Supply includes	Sealing and assembly parts Drilling template
Dimensions	Width: 420 mm Height: 65 mm Depth: 340 mm
Mounting cut-out	Cut-out width: 345 mm Cut-out depth: 265 mm
IP protection category to IEC 60529	IP 43
Note	Via additional installation of the filter holder with filter mat, a protection category of IP 44 is achieved with roof vent 3148.007
Operating temperature range	-10 °C...60 °C
Packs of	1 pc(s).
Net weight	2,644 kg
Gross weight	2,844 kg
Customs tariff number	73269098
ECLASS 8.0	27180716
Product description	SK Roof vent, without fan motor, WHD: 420x65x340 mm