

# Rittal – The System.

Faster – better – everywhere.



## AS 4050.754 Wire end ferrules

State: 18/06/2026 (Source: [rittal.com/rs-sr](http://rittal.com/rs-sr))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# AS 4050.754 - Wire end ferrules loose

With plastic collar.

## Features

Model No.	AS 4050.754
Product description	With plastic collar.
Technical specifications	Heat-resistant to 105 °C
Material	E-Cu, galvanic tin-plated Plastic collar: Polypropylene
Colour	Light blue
Length	8 mm
AWG	24
Internal diameter	1,8 mm
Rittal colour code	Yes
For cross-section	0,25 mm <sup>2</sup>
Note	UL-certified in conjunction with the relevant tools, such as crimping machines. For bespoke advice, please contact your Rittal sales consultant.
Standards	AEH DIN 46228
Delivery form	Loose
Packs of	500 pc(s).
Net weight	0,5 kg
Gross weight	0,026 kg
Customs tariff number	85369010
ETIM 9	EC000005
ETIM 8	EC000005
ECLASS 8.0	36659290

# Features

---

Product description

Wire end ferrules for manual preassembly, 0.25 mm<sup>2</sup>, AWG 24, 8 mm, light blue, loosely packed, 500 pc(s).

# Approvals

---

Approvals

UL + C-UL (listed)  
UR